



# Safety Data Sheet

## Blue Dye FD&C #1 Scienceade Stock Solution

### 1. PRODUCT AND COMPANY IDENTIFICATION

**Product Name:** Blue Dye FD&C #1 Scienceade Stock Solution

**Synonyms/Generic Names:** None

**SDS Number:** NA

**Product Use:** For Educational Use Only

**Manufacturer:** Columbus Chemical Industries, Inc.  
N4335 Temkin Rd.  
Columbus, WI. 53925

**For More Information Contact:** Ward's Science  
5100 West Henrietta Rd.  
PO Box 92912-9012  
Rochester, NY 14692  
(800) 962-2660 (Monday-Friday 7:30-7:00 Eastern Time)

**In Case of Emergency Call:** CHEMTREC - 800-424-9300 or 703-527-3887 (24 Hours/Day, 7 Days/Week)

### 2. HAZARDS IDENTIFICATION

**OSHA Hazards:** No known OSHA hazards.

**Target Organs:** None

**Signal Word:** None

**Pictograms:** None

**GHS Classification:**

Not a hazardous solution according to GHS.

**GHS Label Elements, including precautionary statements:**

**Hazard Statements:**

None

**Precautionary Statements:**

None

#### Potential Health Effects

<b>Eyes</b>	May cause eye irritation.
<b>Inhalation</b>	May be harmful if inhaled. Causes respiratory tract irritation.
<b>Skin</b>	May be harmful if absorbed through skin. Causes skin irritation.
<b>Ingestion</b>	May be harmful if swallowed.

**NFPA Ratings**

Health	0
Flammability	0
Reactivity	0
Specific hazard	Not Available

**HMIS Ratings**

Health	0
Fire	0
Reactivity	0
Personal	E

**3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	Weight %	CAS #	EINECS# / ELINCS#	Formula	Molecular Weight
FD&C Blue #1	<1	3844-45-9	222-339-8	C <sub>37</sub> H <sub>34</sub> N <sub>2</sub> O <sub>9</sub> S <sub>3</sub> Na <sub>2</sub>	792.84 g/mol
Water	>99	7732-18-5	231-791-2	H <sub>2</sub> O	18.00 g/mol

**4. FIRST-AID MEASURES**

<b>Eyes</b>	Rinse with plenty of water for at least 15 minutes.
<b>Inhalation</b>	Move casualty to fresh air and keep at rest. If breathing is difficult, give oxygen. If not breathing, give artificial respiration.
<b>Skin</b>	Flush with plenty of water and wash using soap.
<b>Ingestion</b>	<b>Do Not Induce Vomiting!</b> Never give anything by mouth to an unconscious person. If conscious, wash out mouth with water.

**5. FIRE-FIGHTING MEASURES**

<b>Suitable (and unsuitable) extinguishing media</b>	Product is not flammable. Use appropriate media for adjacent fire. Cool unopened containers with water.
<b>Special protective equipment and precautions for firefighters</b>	Wear self-contained, approved breathing apparatus and full protective clothing, including eye protection and boots.
<b>Specific hazards arising from the chemical</b>	Emits toxic fumes (carbon oxides, nitrogen oxides, sodium oxides, sulfur oxides) under fire conditions. (See also Stability and Reactivity section).

**6. ACCIDENTAL RELEASE MEASURES**

<b>Personal precautions, protective equipment and emergency procedures</b>	See section 8 for recommendations on the use of personal protective equipment.
<b>Environmental precautions</b>	Prevent spillage from entering drains. Any release to the environment may be subject to federal/national or local reporting requirements.
<b>Methods and materials for containment and cleaning up</b>	Pick up and arrange disposal. Sweep up and place in a suitable container for disposal. Clean surfaces thoroughly with water to remove residual contamination. Dispose of all waste and cleanup materials in accordance with regulations.

**7. HANDLING AND STORAGE****Precautions for safe handling**

See section 8 for recommendations on the use of personal protective equipment. Use with adequate ventilation. Wash thoroughly after using. Keep container closed when not in use. Avoid formation of aerosols.

**Conditions for safe storage, including any incompatibilities**

Store in cool, dry well ventilated area. Keep away from incompatible materials (see section 10 for incompatibilities).

---

**8. EXPOSURE CONTROLS / PERSONAL PROTECTION**


---

**Occupational exposure controls:** Contains no substances with occupational exposure limit values.

**Personal Protection**

<b>Eyes</b>	Wear chemical safety glasses or goggles with face shield.
<b>Inhalation</b>	Provide local exhaust, preferably mechanical. If exposure levels are excessive, use an approved respirator.
<b>Skin</b>	Full suit protecting against chemicals.
<b>Other</b>	Not Available

**Other Recommendations**

Provide eyewash stations, quick-drench showers and washing facilities accessible to areas of use and handling.

---

**9. PHYSICAL AND CHEMICAL PROPERTIES**


---

Appearance (physical state, color, etc.)	Blue liquid.
Odor	Not Available
Odor threshold	Not Available
pH	Not Available
Melting point/freezing point	Not Available
Initial boiling point and boiling range	Not Available
Flash point	Not Flammable
Evaporation rate	Not Available
Flammability (solid, gas)	Not Flammable
Upper/lower flammability or explosive limit	Not Explosive
Vapor pressure	Not Available
Vapor density	Not Available
Density	Not Available
Solubility (ies)	Not Available
Partition coefficient: n-octanol/water	Not Available
Auto-ignition temperature	Not Available
Decomposition temperature	Not Available

---

**10. STABILITY AND REACTIVITY**


---

<b>Chemical Stability</b>	Stable
<b>Possibility of Hazardous Reactions</b>	Will not occur.
<b>Conditions to Avoid</b>	Excess heat.
<b>Incompatible Materials</b>	Strong oxidizing agents
<b>Hazardous Decomposition Products</b>	Carbon oxides, nitrogen oxides, sodium oxides, sulfur oxides.

---

## 11. TOXICOLOGICAL INFORMATION

---

### Acute Toxicity

FD&C Blue Dye #1

<b>Skin</b>	Not Available
<b>Eyes</b>	Not Available
<b>Respiratory</b>	Not Available
<b>Ingestion</b>	LD50 Oral- rat- 300 mg/kg

### Carcinogenicity

<b>IARC</b>	No components of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
<b>ACGIH</b>	No components of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.
<b>NTP</b>	No components of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
<b>OSHA</b>	No components of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

### Signs & Symptoms of Exposure

<b>Skin</b>	Skin irritation.
<b>Eyes</b>	Eye irritation.
<b>Respiratory</b>	Irritation.
<b>Ingestion</b>	Irritation.

<b>Chronic Toxicity</b>	Not Available
<b>Teratogenicity</b>	Not Available
<b>Mutagenicity</b>	Not Available
<b>Embryotoxicity</b>	Not Available
<b>Specific Target Organ Toxicity</b>	Not Available
<b>Reproductive Toxicity</b>	Not Available
<b>Respiratory/Skin Sensitization</b>	Not Available

---

## 12. ECOLOGICAL INFORMATION

---

### Ecotoxicity

<b>Aquatic Vertebrate</b>	Not Available
<b>Aquatic Invertebrate</b>	Not Available
<b>Terrestrial</b>	Not Available

<b>Persistence and Degradability</b>	Not Available
<b>Bioaccumulative Potential</b>	Not Available
<b>Mobility in Soil</b>	Not Available
<b>PBT and vPvB Assessment</b>	Not Available
<b>Other Adverse Effects</b>	Not Available

---

## 13. DISPOSAL CONSIDERATIONS

---

<b>Waste Residues</b>	Users should review their operations in terms of the applicable federal/national or local regulations and consult with appropriate regulatory agencies if necessary before disposing of waste product or residues.
<b>Product Containers</b>	Users should review their operations in terms of the applicable federal/national or local regulations and consult with appropriate regulatory agencies if necessary before disposing of waste product containers.

The information offered in section 13 is for the product as shipped. Use and/or alterations to the product may significantly change the characteristics of the material and alter the waste classification and proper disposal methods.

---

#### 14. TRANSPORTATION INFORMATION

---

US DOT	Not Dangerous Goods
TDG	Not Dangerous Goods
IMDG	Not Dangerous Goods
Marine Pollutant	No
IATA/ICAO	Not Dangerous Goods

---

#### 15. REGULATORY INFORMATION

---

TSCA Inventory Status	All ingredients are listed on the TSCA inventory.
DSCL (EEC)	All ingredients are listed on the DSCL inventory.
California Proposition 65	Not Listed
SARA 302	Not Listed
SARA 304	Not Listed
SARA 311	No SARA Hazards
SARA 312	No SARA Hazards
SARA 313	Not Listed
WHMIS Canada	Not Listed

---

#### 16. OTHER INFORMATION

---

Revision	Date
Revision 1	06/06/2013

Disclaimer: Columbus Chemical Industries, Inc. ("Columbus") believes that the information herein is factual but is not intended to be all inclusive. The information relates only to the specific material designated and does not relate to its use in combination with other materials or its use as to any particular process. Because safety standards and regulations are subject to change and because Columbus has no continuing control over the material, those handling, storing or using the material should satisfy themselves that they have current information regarding the particular way the material is handled, stored or used and that the same is done in accordance with federal, state and local law. COLUMBUS MAKES NO WARRANTY, EXPRESS OR IMPLIED, INCLUDING (WITHOUT LIMITATION) WARRANTIES WITH RESPECT TO THE COMPLETENESS OR CONTINUING ACCURACY OF THE INFORMATION CONTAINED HEREIN OR WITH RESPECT TO FITNESS FOR ANY PARTICULAR USE.